



## Wiring Diagram



## Technical Data according to EN 60947-5-2

## Electrical Data

Operational voltage range	$U_B$	10 – 36V DC
Rated insulation voltage	$U_i$	75V DC
Rated impulse withstand voltage	$U_{imp}$	500V
Voltage drop	$U_d$	$\leq 1.5V$ (add. 0.06 V per m cable and 200 mA Load at 20°C)
Utilisation category		DC-13
Rated operational current	$I_e$	$\leq 200mA$
Off-state current	$I_r$	$< 0.3mA$
No-load supply current	$I_0$	$\leq 11mA$
Type of protection		IP 67
Short-circuit protection		pulsed
Rated operating distance	$s_n$	1.5mm
Assured operating distance	$s_a$	0 ... 1.2mm
Repeat accuracy	R	5%
Differential travel (hysteresis)	H	$\approx 10\%$
Switching frequency	f	1000Hz
Switching function		DC, N.O.
Mounting		flush
False polarity protection		yes
Output		permanent overload and s.c.p.
Time delay before availability	$t_v$	$\leq 50ms$

## Elektromagnetic compatibility (EMC)

Electromagnetic field test	IEC 61000-4-3
Electrostatic discharge test	IEC 61000-4-2
Electrical fast transient immunity test	IEC 61000-4-4
Radiated disturbance field strength	EN55011
Impulse voltage withstandability	IEC 255-5

## Mechanical Data

Operating temperature	-25°C ... +70°C
Front cap	PA 6.6, black
Housing	stainless steel (Niro 1.4305)
Indication	LED, yellow
Type of connection	Cable 3 x 0,14mm <sup>2</sup> x 3m; PUR - Outer jacket, black
For attachment	2 x hexagon nut (brass, nickel plated)